



LED-EX torch with batteries, Type: 4AARFL



Order data

Order number	081521 4AARFL
GTIN	032705146035
Item class	08C

Description

Version:

Explosion-proof torch, tested to the applicable ATEX guidelines.

High-performance LED lamps shock-resistant, dust-proof and waterproof.

With **LED reflector technology. LED hand lamp and helmet lamp with special protection technology.** Smooth, wide centre beam. Thanks to the patented optical system, ideal for illuminating wide working areas. Corrosion-resistant. Switch at rear. Easy to attach to work and safety helmet using a helmet holder.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Technical description

Colour of housing	yellow
Battery type	Mignon, AA
IP Index of Protection	IP 67
Head Ø	35 mm
Number of batteries contained	4
ATEX zone	Zone 0
ATEX zone	zone 20
Illumination time	5.5 h
Illumination	225 lm

Weight	158 g
Overall length	158 mm
Tool properties	Suitable for EX areas
Power supply	Battery-powered
Type of product	Flashlight

Accessories

Alkaline-manganese batteries International size LR6	081552 LR6
Alkaline-manganese batteries International size LR6	081554 LR6
Alkaline-manganese batteries International size LR6	081553 LR6
Alkaline-manganese batteries International size LR6	081551 LR6
Lithium-metal batteries International size LR6	081559 LR6
Alkaline-manganese batteries International size LR6	081561 LR6