

**Weidmüller** **Two-pole voltage tester, Type: COMBIPRO****Order data**

Order number	473201 COMBIPRO
GTIN	4032248405749
Item class	47A

**Description****Version:**

Two-pole voltage testers, ergonomic design, plastic housing is waterproof, impact resistant, and unbreakable, two test prods with magnetic clips, suitable for one-hand operation.

**Function:**

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

**Application:**

For professional multi-stage voltage, polarity and continuity testing.

**Standard:**

**IEC / DIN EN 61243-3; VDE 0682-401**

**Supplied with:**

Supplied with 2 batteries 081561 size LR3, thicker test prods (screw-on), insulating protective caps.

**Technical description**

Illumination of probe points	yes
Overvoltage category	CAT III 690 V; CAT IV 600 V

Three phase sequence testing	yes
Calibration	I1
Article no of the battery / rechargeable battery fitted	081551 LR3
Continuity testing	visual / acoustic
IP Index of Protection	IP 65
FI/RCD protective switch test current	yes
Number of batteries contained	2
Manufacturer's designation	VT Combi Pro
Polarity testing	yes
Display range DC	6 - 690 V
Display range AC	6 - 690 V
Display	LED
Power supply	Battery-powered
Power supply	2× 081561 LR3
Type of product	Voltage tester

## Services

CalibrationVoltage tester Type S	027120 S
DAkkS calibrationVoltage tester Type S	027160 S

## Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------