

Weidmüller **Two-pole voltage tester, Type: DIGIPRO****Order data**

Order number	473201 DIGIPRO
GTIN	4032248405756
Item class	47A

Description**Version:**

Two-pole voltage testers, ergonomic design, plastic housing is waterproof, impact resistant, and unbreakable, two test prods with magnetic clips, suitable for one-hand operation. AC voltage tester with true root mean square procedure True RMS. Diode test.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Application:

For professional multi-stage voltage, polarity and continuity testing.

Standard:

IEC / DIN EN 61243-3; VDE 0682-401

Supplied with:

Supplied with 2 batteries 081561 size LR3, thicker test prods (screw-on), insulating protective caps.

Technical description

Display	digital LCD
Display range DC	1 - 1500 V

Three phase sequence testing	yes
Resistance	0 - 1.99 kΩ
Article no of the battery / rechargeable battery fitted	081551 LR3
IP Index of Protection	IP 65
Display range AC	1 - 1000 V
Overvoltage category	CAT III 1,000 V; CAT IV 600 V
FI/RCD protective switch test current	yes
Manufacturer's designation	VT Digi Pro
Polarity testing	yes
Calibration	I1
Number of batteries contained	2
Continuity testing	visual / acoustic
Data storage key	yes
Illumination of probe points	yes
Frequency measurement	1 - 950 Hz
Power supply	Battery-powered
Power supply	2× 081561 LR3
Capacitance	0.05 - 1999 μF
Type of product	Voltage tester

Services

Calibration Voltage tester Type S	027120 S
DAkkS calibration Voltage tester Type S	027160 S

Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------