

Weidmüller **Two-pole voltage tester, Type: MASTER****Order data**

Order number	473201 MASTER
GTIN	4032248405763
Item class	47A

Description**Version:**

Two-pole voltage testers, ergonomic design, plastic housing is waterproof, impact resistant, and unbreakable, two test prods with magnetic clips, suitable for one-hand operation.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Application:

For professional multi-stage voltage, polarity and continuity testing.

Standard:

IEC / DIN EN 61243-3; VDE 0682-401

Supplied with:

Supplied with 2 batteries 081561 size LR3, thicker test prods (screw-on), insulating protective caps.

Technical description

Calibration	11
Polarity testing	yes

Number of batteries contained	2
Display	LED
IP Index of Protection	IP 54
Overvoltage category	CAT III 600 V; CAT IV 300 V
Display range AC	12 - 690 V
Article no of the battery / rechargeable battery fitted	081551 LR3
Display range DC	12 - 690 V
Manufacturer's designation	VT Master
Continuity testing	visual / acoustic
Power supply	Battery-powered
Power supply	2× 081561 LR3
Type of product	Voltage tester

Services

CalibrationVoltage tester Type S	027120 S
DAkkS calibrationVoltage tester Type S	027160 S

Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------