

**Machine / workstation lamp, Type: 5W****Order data**

Order number	081321 5W
GTIN	2050001945921
Item class	08C

Description**Version:**

LED workshop lamps, aluminium black with rocker switch. Rubberised with flex shaft, including magnetic base. LED workshop light, 5 watts with focusable beam angle 15-75°.

Version of the advertising text:

- **Beam dispersion angle 15 – 75°.**

Function:

IP63: Protected against splashed water from directions up to 60° when in normal operating position and protected against penetration by dust (dust-tight), also completely protected against touching.

Note:

In addition to the magnetic base, a screw clamp, wall mounting, table stand and base stand are available.

Technical description

Power supply	Mains-powered
Magnetic base Ø	83 mm

IP Index of Protection	IP 63
Illumination	450 lm
Lamp replaceable	no
Light output	5 W
Nominal voltage	250 V
Overall height	480 mm
Type of product	Desk lamp / workstation lamp