



Machine / workstation lamp, Type: 6WDUO



Order data

Order number	081321 6WDUO
GTIN	2050001945938
Item class	08C

Description

Version:

LED workshop lamps, aluminium black with rocker switch. Rubberised with flex shaft, including magnetic base. LED workshop light 2 × 6 watts, light head with two 360° rotating light modules in the light head.

Function:

IP63: Protected against splashed water from directions up to 60° when in normal operating position and protected against penetration by dust (dust-tight), also completely protected against touching.

Note:

In addition to the magnetic base, a screw clamp, wall mounting, table stand and base stand are available.

Technical description

IP Index of Protection	IP 63
Magnetic base Ø	83 mm
Illumination	1200 lm

Power supply	Mains-powered
Lamp replaceable	no
Light output	12 W
Nominal voltage	250 V
Overall height	510 mm
Type of product	Desk lamp / workstation lamp