

**LED torch, Type: P7****Order data**

Order number	081485 P7
GTIN	4058205009898
Item class	04B

**Description****Version:**

High-performance line of LED LENSER for general- purpose use. Drop tested from a 1 m height. LED lenses are amongst the technology leaders for LED torches. Within the **splash-proof aluminium housing**, all the contacts are gold-plated, **high-quality lenses** gather the light uniformly and without losses. All these high-class torches incorporate the patented **Advanced Focus System**.

- **Advanced Focus System (AFS)**

**The Advanced Focus System is a combination of lens and reflector, thus incorporating the advantages of both systems. The result is an outstanding concentration of light in focus, together with a largely homogeneous unfocussed light beam. This makes the AFS one of the best focussing systems in the world for LED lamps.**

- **Rapid Focus**

**Conventional focussing systems with twist knobs must be operated manually with both hands. Rapid Focus, on the other hand, allows quick adjustment of the light beam with only one hand.**

**Function:**

IPX4: Protected against splashed water from all directions, but without any protection against foreign bodies or touching.

**Supplied with:**

Including battery No. 081557 LR3.

**Technical description**

Weight	175 g
--------	-------

Number of batteries contained	4
Manufacturer's designation	P7
Advanced Focus System (AFS)	yes
Head Ø	37 mm
Illumination	450 lm
IP Index of Protection	IP X4
Illumination step 2	40 lm
Illumination time	25 h
Including belt pocket	yes
Rapid Focus	yes
Illumination time stage 2	25 h
Overall length	130 mm
Power supply	Battery-powered
International size	LR3
Type of product	Flashlight