

**Garant****All-steel clamp, Jaw capacity: 300mm****Order data**

Order number	860480 300
GTIN	4045197167446
Item class	81D

**Description****Version:**

Beam / fixed jaw made of bright drawn steel, moving jaw of forged steel, each hardened and electro galvanised. Smooth running steel spindle with trapezoidal thread, burnished. Moving jaw with integral **spindle locking prevents the release** of the spindle even in case of vibrations. Maximum force transfer due to **power grip** with handy Haptoprene® surface and impact resistant PP core. Surface structure is anti-slip even with wet, oily hands.  
Cross section of the slide rail: 25×12 mm  
Throat: 140 mm

**Technical description**

Jaw capacity	300 mm
Throat	140 mm
Cross section of the slide rail	25×12 mm
Type of product	Clamp

