

**Garant**
**All-steel clamp, Jaw capacity: 400mm**

**Order data**

Order number	860480 400
GTIN	4045197167453
Item class	81D

**Description**
**Version:**

Beam / fixed jaw made of bright drawn steel, moving jaw of forged steel, each hardened and electro galvanised. Smooth running steel spindle with trapezoidal thread, burnished.

Moving jaw with integral **spindle locking prevents the release** of the spindle even in case of vibrations. Maximum force transfer due to **power grip** with handy Haptoprene® surface and impact resistant PP core. Surface structure is anti-slip even with wet, oily hands.

Cross section of the slide rail: 25×12 mm

Throat: 120 mm

**Technical description**

Jaw capacity	400 mm
Cross section of the slide rail	25×12 mm
Throat	120 mm
Type of product	Clamp

