

**All-steel clamp, Jaw capacity: 800mm****Order data**

| | |
|--------------|---------------|
| Order number | 860500 800 |
| GTIN | 4008158034232 |
| Item class | 83K |

Description**Version:**

Beam / fixed jaw made of bright drawn steel, moving jaw of forged steel, each hardened and electro galvanised. Smooth running steel spindle with trapezoidal thread, burnished. Movable pressure pad from size 160 can be exchanged without tools. Clamping force of up to 6000 N.

Technical description

| | |
|---------------------------------|----------|
| Cross section of the slide rail | 28×11 mm |
| Jaw capacity | 800 mm |
| Throat | 120 mm |
| Type of product | Clamp |

Accessories

Pressure plate assortment 8 pieces Pressure pad Ø 37 mm

860115 37