



## Sheet metal drill HSS single-sided, uncoated, Ø DC h8: 3,2mm



### Order data

Order number	113341 3,2
GTIN	4045197964250
Item class	12B

### Description

#### Version:

**Extremely break-resistant** due to short helix and strong core taper. Self-centring point.

**Cylindrically ground on circumference**(without chamfers) to prevent jamming.

Vaporised surface.

Dimensions similar to DIN 1897.

Point geometry shape C.

#### Application:

**Especially for drilling sheet metal.**

### Technical description

Overall length L	49 mm
Standard	DIN 1897
Tolerance nominal Ø	h8
recommended maximum drilling depth L <sub>2</sub>	7.2 mm
Flute length L <sub>c</sub>	12 mm
Nominal Ø D <sub>c</sub>	3.2 mm
Number of cutting edges Z	2
Point angle	135 degrees
Coating	uncoated
Tool material	HSS
Through-coolant	no

Colour ring	without
Type of product	Jobber drill

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Alu plastics	suitable only under restricted conditions		
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm <sup>2</sup>	suitable		
Steel < 750 N/mm <sup>2</sup>	suitable only under restricted conditions		
dry	suitable		