

Garant**All-steel clamp, Jaw capacity: 600mm****Order data**

Order number	860480 600
GTIN	4045197167477
Item class	81D

Description**Version:**

Beam / fixed jaw made of bright drawn steel, moving jaw of forged steel, each hardened and electro galvanised. Smooth running steel spindle with trapezoidal thread, burnished.

Moving jaw with integral **spindle locking prevents the release** of the spindle even in case of vibrations. Maximum force transfer due to **power grip** with handy Haptoprene® surface and impact resistant PP core. Surface structure is anti-slip even with wet, oily hands.

Cross section of the slide rail: 25×12 mm

Throat: 120 mm

Technical description

Throat	120 mm
Jaw capacity	600 mm
Cross section of the slide rail	25×12 mm
Type of product	Clamp

