



## Drill chuck with keyless locking Metal version, Type: 13-3/8



### Order data

Order number	342207 13-3/8
GTIN	4045197966018
Item class	32W

### Description

#### Version:

- **Keyless drill chuck with self-tightening locking mechanism. No additional locking required (not even for impact drilling).**
- **Very ergonomic, user-friendly, hexagon flats for wrench assistance.**
- **Good concentricity.**
- **Through hole version for right-hand and left-hand operation (thread M5 or M6).**

Special clamping chamfer for wear reduction.

Clamping range: 1.5 - 13 mm

External Ø: 43.1 mm

Drill head length open: 63 mm

Drill head length closed: 74 mm

Adapter: 3/8-24 in

maximum machine power: 1100 W

### Technical description

Type	13-3/8
Clamping range	1.5 - 13 mm
Drill head length open	63 mm
maximum machine power	1100 W

Drill head length closed	74 mm
External Ø	43.1 mm
Adapter	3/8-24 in
Keyless locking mechanism	yes
Type of product	Drill chuck keyless