

**All-steel clamp, Jaw capacity: 100mm****Order data**

Order number	860500 100
GTIN	4008158033778
Item class	83K

**Description****Version:**

Beam / fixed jaw made of bright drawn steel, moving jaw of forged steel, each hardened and electro galvanised. Smooth running steel spindle with trapezoidal thread, burnished. Movable pressure pad from size 160 can be exchanged without tools. Clamping force of up to 6000 N.

**Technical description**

Cross section of the slide rail	15×6 mm
Jaw capacity	100 mm
Throat	60 mm
Type of product	Clamp

**Accessories**

Pressure plate assortment 8 pieces Pressure pad Ø 23 mm

860115 23