



Profile slotting toolholder for square cutting inserts \varnothing D1 20 mm, from square: 16 mm



Order data

Order number	290330 16
GTIN	4045197965318
Item class	21U

Description

Version:

Very high stability due to the full length support from the insert pocket to the shank.

Note:

- **For machining centres, use the alignment aid No. 290397 and a dial indicator to check the spindle orientation.**
- **For lathes without Y-axis, please use eccentric bush No. 290391– 290393 for exact setting of the Y-coordinate.**

Through-coolant: ja

Shank length L_s : 50 mm

suitable for square drive: 16 - 19 mm

Usable length L_N : 52 mm

Centre-line offset: 8.5 mm

Min. pre-drilling $-\varnothing D_{min}$: 16 mm

Screw: 290399 3

Technical description

Centre-line offset	8.5 mm
Screw	290399 3
Usable length L_N	52 mm
Min. pre-drilling $-\varnothing D_{min}$	17.2 mm
suitable for square drive	17 - 19 mm
Shank \varnothing	20 mm

Tool holder $\varnothing D_2$	16 mm
Through-coolant	yes
Shank length L_s	50 mm