



## Profile slotting toolholder for square cutting inserts $\varnothing$ D1 32 mm, from square: 13 mm



### Order data

Order number	290334 13
GTIN	4045197965431
Item class	21U

### Description

#### Version:

Very high stability due to the full length support from the insert pocket to the shank.

#### Note:

- **For machining centres, use the alignment aid No. 290397 and a dial indicator to check the spindle orientation.**
- **For lathes without Y-axis, please use eccentric bush No. 290391– 290393 for exact setting of the Y-coordinate.**

Through-coolant: ja

Shank length  $L_s$ : 100 mm

suitable for square drive: 13 - 16 mm

Usable length  $L_N$ : 50 mm

Centre-line offset: 7 mm

Min. pre-drilling  $-\varnothing D_{min}$ : 13 mm

Screw: 290399 2

### Technical description

Screw	290399 2
Centre-line offset	7 mm
Min. pre-drilling $-\varnothing D_{min}$	14.2 mm
Usable length $L_N$	50 mm
suitable for square drive	14 - 16 mm
Shank $\varnothing$	32 mm

Tool holder $\varnothing D_2$	13 mm
Through-coolant	yes
Shank length $L_s$	100 mm