

Garant
Profile slotting toolholder for hexagon cutting inserts \varnothing DS 25 mm, from hexagon: 28mm

Order data

| | |
|--------------|---------------|
| Order number | 290342 28 |
| GTIN | 4045197965639 |
| Item class | 29K |

Description
Note:

- For machining centres, use the pull-up aid No. 290397 and a dial indicator to check the spindle orientation.
- For lathes without Y-axis, please use eccentric bush No. 290391 – 290393 for exact setting of the Y-coordinate.

Technical description

| | |
|---|--|
| Centre offset L_3 | 14 mm |
| Screw | 290399 3 |
| Min. pre-drilling $-\varnothing D_{\min}$ | 26.5 mm |
| Reach L_1 | 89 mm |
| suitable for hexagon drive | 28 - 37 mm |
| Shank \varnothing | 25 mm |
| Tool holder $\varnothing D_1$ | 25 mm |
| Through-coolant | yes |
| Shank length L_s | 90 mm |
| Shank | Combination shank |
| Type of product | Keyway broaching and profile slotting tool |

