

Garant
Profile slotting toolholder for hexagon cutting inserts \varnothing DS 20 mm, from hexagon: 17mm

Order data

Order number	290340 17
GTIN	4045197965578
Item class	29K

Description
Note:

- For machining centres, use the pull-up aid No. 290397 and a dial indicator to check the spindle orientation.
- For lathes without Y-axis, please use eccentric bush No. 290391 – 290393 for exact setting of the Y-coordinate.

Technical description

Screw	290399 2
Reach L_1	56 mm
Centre offset L_3	8.5 mm
Min. pre-drilling $-\varnothing D_{\min}$	16 mm
suitable for hexagon drive	17 - 28 mm
Shank \varnothing	20 mm
Tool holder $\varnothing D_1$	15 mm
Through-coolant	yes
Shank length L_s	50 mm
Shank	Combination shank
Type of product	Keyway broaching and profile slotting tool

