

**Garant**
**Profile slotting toolholder for hexagon cutting inserts  $\varnothing$  DS 25 mm, from hexagon: 11 mm**

**Order data**

Order number	290342 11
GTIN	4045197965615
Item class	29K

**Description**
**Note:**

- For machining centres, use the pull-up aid No. 290397 and a dial indicator to check the spindle orientation.
- For lathes without Y-axis, please use eccentric bush No. 290391 – 290393 for exact setting of the Y-coordinate.

**Technical description**

Centre offset $L_3$	5.5 mm
Screw	290399 1
Min. pre-drilling $-\varnothing D_{\min}$	10.5 mm
Reach $L_1$	40 mm
suitable for hexagon drive	11 - 17 mm
Shank $\varnothing$	25 mm
Tool holder $\varnothing D_1$	10 mm
Through-coolant	yes
Shank length $L_s$	90 mm
Shank	Combination shank
Type of product	Keyway broaching and profile slotting tool

