



## All-steel high-performance clamp with special jaw anvil, Jaw capacity: 250mm



### Order data

Order number	861100 250
GTIN	4008158007229
Item class	83K

### Description

#### Version:

Beam and fixed jaw made of bright steel section (special profile), tempered and electro-galvanised. Slide jaw made of steel, drop-forged, tempered, and electro-galvanised. Wear-resistant smooth-running steel spindle with trapezoidal thread. Long working life due to heat-resistant special pressure pad with sintered steel inlay, can tilt through 35°. Spindle tempered and burnished with adjustable clamp handle.

#### Application:

For heaviest duty clamping of workpieces in steel construction, blacksmith's shops, HGV bodywork, machine tool manufacture etc. The movable special jaw anvil permits clamping diagonal workpieces up to 35°. **Maximum clamping pressure up to approx. 12000 N.**

### Technical description

Cross section of the slide rail	34x13 mm
Throat	140 mm
Weight	2.5 kg
Jaw capacity	250 mm

Type of product

Clamp

---

**Accessories**

Spindle with tightening bar and pressure plate

861140

Pressure plate including fastenings

861130