

**Garant****All-steel clamp, Jaw capacity: 1250mm****Order data**

Order number	860480 1250
GTIN	4045197167507
Item class	81D

**Description****Version:**

Beam / fixed jaw made of bright drawn steel, moving jaw of forged steel, each hardened and electro galvanised. Smooth running steel spindle with trapezoidal thread, burnished.

Moving jaw with integral **spindle locking prevents the release** of the spindle even in case of vibrations. Maximum force transfer due to **power grip** with handy Haptoprene® surface and impact resistant PP core. Surface structure is anti-slip even with wet, oily hands.

Cross section of the slide rail: 27×13 mm

Throat: 120 mm

**Technical description**

Cross section of the slide rail	27×13 mm
Jaw capacity	1250 mm
Throat	120 mm
Type of product	Clamp

