



## All-steel lever clamp, Jaw capacity: 120mm



### Order data

Order number	860600 120
GTIN	4008158034324
Item class	83K

### Description

#### Version:

Beam / fixed jaw made of bright drawn steel, moving jaw of forged steel, each hardened and electro galvanised. Clamping lever with self-locking ratchet clamping mechanism. Opens by releasing the ratchet. Movable pressure pad, clamping lever powder coated.

Maximum clamping force: up to 8500 N.

#### Application:

For **fast** and easy **clamping with high clamping pressure**.

### Technical description

Weight	0.5 kg
Cross section of the slide rail	15×6 mm
Throat	60 mm
Jaw capacity	120 mm
Type of product	Clamp

