

Garant**All-steel clamp, Jaw capacity: 120mm****Order data**

Order number	860480 120
GTIN	4045197335067
Item class	81D

Description**Version:**

Beam / fixed jaw made of bright drawn steel, moving jaw of forged steel, each hardened and electro galvanised. Smooth running steel spindle with trapezoidal thread, burnished.

Moving jaw with integral **spindle locking prevents the release** of the spindle even in case of vibrations. Maximum force transfer due to **power grip** with handy Haptoprene® surface and impact resistant PP core. Surface structure is anti-slip even with wet, oily hands.

Cross section of the slide rail: 13.5×6.5 mm

Throat: 60 mm

Technical description

Jaw capacity	120 mm
Cross section of the slide rail	13.5×6.5 mm
Throat	60 mm
Type of product	Clamp

