

**All-steel clamp, Jaw capacity: 200mm****Order data**

Order number	860500 200
GTIN	4008158033914
Item class	83K

**Description****Version:**

Beam / fixed jaw made of bright drawn steel, moving jaw of forged steel, each hardened and electro galvanised. Smooth running steel spindle with trapezoidal thread, burnished. Movable pressure pad from size 160 can be exchanged without tools. Clamping force of up to 6000 N.

**Technical description**

Jaw capacity	200 mm
Throat	100 mm
Cross section of the slide rail	22×8.5 mm
Type of product	Clamp

**Accessories**

Pressure plate assortment 8 pieces Pressure pad Ø 30 mm	860115 30
Complete lower section for all-steel screw clamps Type 200	860560 200