

Garant**All-steel clamp with fold-out handle, Jaw capacity: 200mm****Order data**

Order number	860490 200
GTIN	4045197604262
Item class	81D

Description**Version:**

Beam / fixed jaw made of bright drawn steel, moving jaw of forged steel, each hardened and electro galvanised. Smooth running steel spindle with trapezoidal thread, burnished.

Moving jaw with integral **spindle locking prevents the release** of the spindle even in case of vibrations. Maximum force transfer due to **power grip** with handy Haptoprene® surface and impact resistant PP core. Surface structure is anti-slip even with wet, oily hands.

All-steel clamp with fold-out handle. Quick approach and clamping of the workpiece with the handle engaged in the vertical position. **Powerful and convenient working with the handle folded out.**

Cross section of the slide rail: 19.5×9.5 mm

Throat: 100 mm

Technical description

Throat	100 mm
Jaw capacity	200 mm
Cross section of the slide rail	19.5×9.5 mm

Type of product

Clamp