

Garant
All-steel clamp, Jaw capacity: 160mm

Order data

Order number	860480 160
GTIN	4045197167415
Item class	81D

Description
Version:

Beam / fixed jaw made of bright drawn steel, moving jaw of forged steel, each hardened and electro galvanised. Smooth running steel spindle with trapezoidal thread, burnished.

Moving jaw with integral **spindle locking prevents the release** of the spindle even in case of vibrations. Maximum force transfer due to **power grip** with handy Haptoprene® surface and impact resistant PP core. Surface structure is anti-slip even with wet, oily hands.

Cross section of the slide rail: 16×7,5 mm

Throat: 80 mm

Technical description

Cross section of the slide rail	16×7,5 mm
Jaw capacity	160 mm
Throat	80 mm
Type of product	Clamp

