



All-steel high-performance clamp with special jaw anvil, Jaw capacity: 800mm



Order data

Order number	861100 800
GTIN	4008158007366
Item class	83K

Description

Version:

Beam and fixed jaw made of bright steel section (special profile), tempered and electro-galvanised. Slide jaw made of steel, drop-forged, tempered, and electro-galvanised. Wear-resistant smooth-running steel spindle with trapezoidal thread. Long working life due to heat-resistant special pressure pad with sintered steel inlay, can tilt through 35°. Spindle tempered and burnished with adjustable clamp handle.

Application:

For heaviest duty clamping of workpieces in steel construction, blacksmith's shops, HGV bodywork, machine tool manufacture etc. The movable special jaw anvil permits clamping diagonal workpieces up to 35°. **Maximum clamping pressure up to approx. 12000 N.**

Technical description

Throat	140 mm
Cross section of the slide rail	34×13 mm
Weight	4.4 kg
Jaw capacity	800 mm

Type of product	Clamp
-----------------	-------

Accessories

Pressure plate including fastenings	861130
Spindle with tightening bar and pressure plate	861140