



Safety helmet BOP 74 R, Colour: BLUE



Order data

Order number	097801 BLUE
GTIN	4017765057350
Item class	09K

Description

Version:

The **high-performance all-round helmet** of glass fibre polyester offers high lateral stiffness and keeps its shape well particularly at high temperatures. Reaches well down on to the neck with a large protective area. The helmet has a high resistance to ageing and is resistant to chemicals. Protection against splashes of liquid metal (MM), and against side deformation (LD).

- **6-point strap attachment, height adjustable**
- **Without mounting**
- **Natural leather sweatband**
- **Pulled-down neck with rain gutter**
- **With rotary catch**

Application:

Hot operations, chemical industry, workstations with high UV radiation.

Standard:

DIN EN 397

Specification:

Protection against splashes of liquid metal (MM), and against side deformation (LD).

Spare part:

No. 097822 sweatbands in three different versions.

Helmet characteristics: Protection against lateral deformation

Material of helmet shell: UP-GF glass fibre-polyester

Lens coating: resistant to chemicals

Width adjustment: Drejelukning

Size: 53 - 61 cm

Weight: 460 g

Technical description

Size	53 - 61 cm
Lens coating	resistant to chemicals
Weight	460 g
Width adjustment	Drejelukning
Helmet characteristics	Beskyttelsesegenskab indtil 150°C
Helmet characteristics	Protection against liquid metal spraying out
Helmet characteristics	Protection against lateral deformation
Material of helmet shell	UP-GF glass fibre-polyester
Standard	DIN EN 397
Type of product	Safety helmet

Accessories

Sweatband Type HT	097822 HT
Sweatband Type SL	097822 SL
Sweatband Type L	097822 L