

**All-steel clamp, Jaw capacity: 300mm****Order data**

Order number	860500 300
GTIN	4008158034119
Item class	83K

**Description****Version:**

Beam / fixed jaw made of bright drawn steel, moving jaw of forged steel, each hardened and electro galvanised. Smooth running steel spindle with trapezoidal thread, burnished. Movable pressure pad from size 160 can be exchanged without tools. Clamping force of up to 6000 N.

**Technical description**

Cross section of the slide rail	28×11 mm
Throat	140 mm
Jaw capacity	300 mm
Type of product	Clamp

**Accessories**

Complete lower section for all-steel screw clamps Type 300	860560 300
Pressure plate assortment 8 pieces Pressure pad Ø 37 mm	860115 37