

## Garant

### Flap disc (ZA), Ø 50.8 mm, Grit: 60



## Order data

Order number	554032 60
GTIN	4045197966735
Item class	51E

## Description

### Version:

Compared to conventional grinding discs, **mini-flap discs** with abrasive strips arranged at a very steep angle offer a **longer working life, more flexible grinding characteristics** and a **more even surface finish** (roughness value) down to the wear limit.

The **quick-change system** (Roloc™, Combidisc® CDR) with a plastic external thread permits safe abrasive tool changing "with a single twist of the wrist" in a very short time.

Flat, compact arrangement of the strips for **weld seam dressing** and for **deburring work**.

### Application:

For efficient abrasion of small areas, even with changing contours. Reduced tool changing times save costs on multi-stage operations.

### Note:

**Roloc™ bristle discs** can be found from No. 573510 onwards.

## Technical description

Disc Ø	50.8 mm
Grit	60
Grinding medium code	ZA
Product name attribute	Ø 50.8 mm

maximum speed	19100 min <sup>-1</sup>
Type of product	Abrasive flap disc

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable only under restricted conditions		
dry	suitable		