

HOLEX**All-steel high-performance clamp with special jaw anvil, Jaw capacity: 250mm****Order data**

Order number	861120 250
GTIN	4045197657381
Item class	82C

Description**Version:**

Beam and fixed jaw made of bright steel section (special profile), tempered and electro-galvanised. Slide jaw made of steel, drop-forged, tempered, and electro-galvanised. Wear-resistant smooth-running steel spindle with trapezoidal thread. Long working life due to heat-resistant special pressure pad with sintered steel inlay, can tilt through 35°. Spindle tempered and burnished with adjustable clamp handle.

Application:

For heaviest duty clamping of workpieces in steel construction, blacksmith's shops, HGV bodywork, machine tool manufacture etc. The movable special jaw anvil permits clamping diagonal workpieces up to 35°. **Maximum clamping pressure up to approx. 12000 N.**

Technical description

Cross section of the slide rail	30×15 mm
Throat	140 mm
Jaw capacity	250 mm
Weight	2.8 kg

Type of product

Clamp

Accessories

Pressure plate Type GSP

861121 GSP

Pressure plate Type GSV

861121 GSV