



Fresh air welder's mask, automatic optrel® vegaview2.5, Colour: AIR



Order data

| | |
|--------------|---------------|
| Order number | 097977 AIR |
| GTIN | 7640127615898 |
| Item class | 09U |

Description

Version:

Lightweight welder's mask, automatic (482 g) for low stress on the head and neck muscles. With the best view and **100% protection against UV and IR radiation**. The mask has **true colour-rendition** and a shade level in the light state with high translucency of 23%, allowing a detailed clear view of the component. Simply pushing a button on the outside activates **grinding mode**. Ideal for poorly lit working environments. With comfortable headband with adjustment facility. The angle of perception of the electric arc can be adjusted using a slider; the sensitivity can also be adjusted for an ideal match to the working environment.

- **Shade levels: 8 – 12**
- **Shade level in the light state: 2.5**
- **With lithium 3 V battery (working life 3,000 hours)**
- **Field of view of the welding filter: 50 x 100 mm**

The fresh air supply to the optrel® vegaview2.5 has the same product characteristics as the standard version No. 097949 size BLACK. With a few simple movements of the hand the helmet can be connected to the **optrel® e3000X No. 097978 size E3000X respirator system with blower unit**.

Application:

MIG/MAG welding. Stick welding, TIG welding, plasma welding and cutting

Standard:

EN 175; EN 379; EN 166

Suitable for:

No. 097978 size E3000 **optrel® e3000** respirator system with blower unit.

Supplied with:

1 outer visor, 1 storage bag

Technical description

| | |
|---|-----------------|
| Classification to EN 379 | 1 / 1 / 1 / 2 |
| Switching time from dark to bright | 50 - 1000 ms |
| Number of batteries contained | 1 |
| Article no of the battery / rechargeable battery fitted | 081560 CR2032 |
| Switching time from bright to dark | 0.1 ms |
| Power supply | Battery-powered |
| Type of product | Welder's mask |