

Garant
Burr Z FINE – very fine, Carbide, Type: M0618

Order data

Order number	540440 M0618
GTIN	4045197966780
Item class	51D

Description
Version:

 Shank \varnothing 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Pointed cone shape** (SKM).

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Shank \varnothing	6 mm
Shape description	pointed cone
Toothing grit designation	very fine
Shape	M0618
Overall length	50 mm
Head \varnothing	6 mm
Tooth type abbreviation	Z FINE
Head length	18 mm
Series	Tooth configuration Z FINE
Tool material	Carbide

Type of product

Burr

User data

	Suitability	V_c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		