

**Garant****Burr Z7 – medium, diamond cut, Carbide, Type: E1220****Order data**

Order number	540200 E1220
GTIN	4045197967305
Item class	51D

**Description****Version:**

Shank Ø 6 mm.

**GARANT** burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

**Application:**

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: teardrop

Head Ø: 12 mm

Head length L<sub>1</sub>: 20 mm

Overall length: 60 mm

Shank Ø: 6 mm

**Technical description**

Head Ø	12 mm
--------	-------

Shape description	teardrop
Toothing grit designation	medium
Type of cut	staggered teeth
Tooth type abbreviation	Z7
Shank Ø	6 mm
Head length L <sub>1</sub>	20 mm
Shape	E1220
Overall length	60 mm
Tool material	Carbide
Type of product	Burr