

**Garant****Burr Z7 – medium, diamond cut, Carbide, Type: H1230****Order data**

Order number	540200 H1230
GTIN	4045197967329
Item class	51D

**Description****Version:**

Shank Ø 6 mm.

**GARANT** burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

**Application:**

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: flame

Head Ø: 12 mm

Head length L<sub>1</sub>: 30 mm

Overall length: 70 mm

Shank Ø: 6 mm

**Technical description**

Head Ø	12 mm
--------	-------

Toothing grit designation	medium
Shape description	flame
Shape	H1230
Overall length	70 mm
Head length L <sub>1</sub>	30 mm
Type of cut	staggered teeth
Tooth type abbreviation	Z7
Shank Ø	6 mm
Tool material	Carbide
Type of product	Burr