

Flat magnet 2-part set with threaded socket flat, Neodymium, Ø: 22mm



Order data

| | |
|--------------|---------------|
| Order number | 085931 22 |
| GTIN | 5012095615118 |
| Item class | 08Q |

Description

Version:

- **Shielded flat magnet with 3 to 6 times the clamping force compared to hard ferrite magnets.**
- **Corrosion resistance and surface protection due to the rubberised surface.**
- **Rubberisation increases the lateral holding forces.**
- **Neodymium magnetic core.**

Application:

On painted surfaces, will not scratch or slip.

Note:

Screw-in hooks with external thread under No. 085921.

Technical description

| | |
|-----------------------------|---------------------|
| Thread | M4 mm |
| Height with thread | 6 mm |
| Nominal clamping force | 50 N |
| Height | 6 mm |
| Material of the magnet core | Neodymium |
| Type of product | Flat gripper magnet |

Accessories

Screw-in hook set with external thread 10 pieces Thread M4

085921 M4