

## Flat magnet 2-part set with threaded socket flat, Neodymium, Ø: 66mm



### Order data

Order number	085931 66
GTIN	5012095615132
Item class	08Q

### Description

#### Version:

- **Shielded flat magnet with 3 to 6 times the clamping force compared to hard ferrite magnets.**
- **Corrosion resistance and surface protection due to the rubberised surface.**
- **Rubberisation increases the lateral holding forces.**
- **Neodymium magnetic core.**

#### Application:

On painted surfaces, will not scratch or slip.

#### Note:

Screw-in hooks with external thread under No. 085921.

### Technical description

Height with thread	8.5 mm
Thread	M5 mm
Nominal clamping force	180 N
Height	8.5 mm
Material of the magnet core	Neodymium
Type of product	Flat gripper magnet

---

## Accessories

Screw-in hook set with external thread 10 pieces Thread M5

085921 M5