

# Manual hydraulic device with pivoting cylinder in a sheet metal case, Type: 1



### **Order data**

Order number	834655 1
GTIN	4045197967244
Item class	86C

## **Description**

#### **Version:**

Manual hydraulic with pressure rating up to approx. 600 bar, with multiple movement cylinder (can be rotated and swivelled through 360°), with 3/4−16 UNF thread suitable for draw bolts No. 834070. Aluminium pivot head and cylinder combination, very light in weight.

Punching power: For round sheet metal punches and swarf punches up to Ø 82 / thickness 3 mm / St 37 or larger for thinner and weaker materials. Case L×W×H: 495×385×140 mm.

### **Application:**

For powering sheet metal punches.

#### Note:

When ordering the hydraulic drive, please order the **draw bolts No. 834070 necessary** for the round sheet metal punches!

# **Technical description**

Case length	495 mm
Case width	385 mm
Case height	140 mm
Type of product	Punching tool