

**HOLEX**

## Round sheet metal punch set "UNF" Ø 16.2 – 63.5 mm in a sheet metal case, Type: 1



### Order data

Order number	834555 1
GTIN	4045197967169
Item class	86C

### Description

#### Version:

Matrix punches and pressure screws with UNF fine thread. With ball thrust bearing draw bolts to reduce the friction. Compatible with all the main manufacturers of sheet metal punches with UNF threads.

#### Supplied with:

1 each punch and matrix for hole Ø 16.2 (for M16); 20.4 (for M20 and PG13); 22.5 (for M22 and PG16); 25.4 (for M25); 32.5 (for M32); 40.5 (for M40); 50.5 (for M50); 63.5 (for M63).

Ø 16.2 – 25.4 with 3/8 inch UNF thread and Ø 32.5 – 63.5 with 3/4 inch UNF thread.

2 ball bearing draw bolts **3/8 inch – UNF**, 40 mm.

1 ball bearing draw bolt **3/4 inch – UNF**, 52 mm.

1 ball bearing draw bolt **3/4 inch – UNF**, 65 mm.

1 HSS stepped drill (Ø 6 – 21 mm).

1 robust plastic case, size 340×280×90 mm.

### Technical description

Type of product	Punching tool
-----------------	---------------

