



Climate measuring instrument, Type: 440



Order data

Order number	474141 440
GTIN	4029547019289
Item class	47B

Description

Version:

testo 440 multi-function measuring device for measurement of temperature, moisture, pressure, air flow, illumination intensity, CO, and CO₂.

- **Intuitive and clearly structured measurement menus with high user comfort.**
- **Comprehensive selection of climatic probes for a wide range of applications.**
- **Probe handles with cable or Bluetooth connections. Can be used universally for all probes.**
- **Clear parallel display of 3 values.**
- **Internal memory for up to 7500 measurement reports**

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

3 batteries No. 081561 size LR6, USB cable and calibration certificate.

Optional extras:

Optional accessories: Probes No. 474144 / 474146 / 474148 / 474152 / 474156 / 474157 and case No. 474161.

Note:

Testo 440 dp with differential pressure sensor **for flow measurements in air containing particles (pitot tube measurements). Other probes** (with cable or Bluetooth connections) and **sets available on request for any application.**

Calibration: Price on request

IP Index of Protection: IP 54

Weight: 250 g

Length: 154 mm

Width: 65 mm

Height: 32 mm

Technical description

Article no of the battery / rechargeable battery fitted	081561 LR6
Number of batteries contained	3
Weight	250 g
Length	154 mm
Width	65 mm
Height	32 mm
Power supply	Battery-powered
IP Index of Protection	IP 54
Interface	Bluetooth interface
Interface	USB interface
Device memory	7500 measurement reports
Calibration	Price on request
Type of product	Climate measuring instrument

Accessories

Flow rate sensor Type FR	474152 FR
Air temperature sensors Type NTC	474144 NTC
Alkaline-manganese batteries International size LR6	081561 LR6
Humidity and temperature sensors with cable connection Type FT	474146 FT

Lux probe Type LUX	474158 LUX
Humidity and temperature sensors with Bluetooth connection Type FT	474148 FT
Alkaline-manganese batteries International size LR6	081556 LR6
CO2 probe Type CO2	474156 CO2
Flow rate sensor Type HD	474152 HD
Case Type K	474161 K