



Humidity and temperature sensors with cable connection, Type: FT



Order data

Order number	474146 FT
GTIN	4029547019043
Item class	47B

Description

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Technical description

Error limit temperature	$\pm 0.5\text{ }^{\circ}\text{C}$
Relative humidity measurement range	0 - 100 %
Error limit relative humidity	$\pm 2\text{ }%$
Temperature measurement range	-20 - 70 $^{\circ}\text{C}$
IP Index of Protection	IP 54
Calibration	I6
Interface	Bluetooth interface
Type of product	Humidity and temperature sensor

Services

CalibrationThermo-hygrometer Type A	027660 A
DAkkS calibrationThermo-hygrometer Type A	027670 A