



Flow rate sensor, Type: FR



Order data

Order number	474152 FR
GTIN	4029547018916
Item class	47B

Description

Version:

Impeller measurement probe \varnothing 16 mm for measuring large airflows up to 50 m/s. Telescopic extension up to 850 mm long allows measurements in pipes or ducts.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Technical description

Measuring range	0.6 - 50 m/s
Error limit (m/s + % of measured value)	$\pm 0.2 + 1\%$ (0.6 to 40 m/s) $\pm 0.2 + 2\%$ (40.1 to 50 m/s) m/s
Operating temperature	-10 - 70 °C
IP Index of Protection	IP 54
Power supply	Mains operated
Type of product	Flow rate sensor

