



FlyMarker® mini 120/45 needle marker Cordless, Battery capacity: 2X2 Ah

Order data

Order number	085761 2X2
GTIN	2050001945983
Item class	04F

Description

Version:

- Supplied with an HPGL package (for marking individual logos and inspection symbols, CE marks etc.)
- Supplied with a convenience package (e.g. for shift identification, pre-positioning, multiple marking, etc.)
- Internal memory for several hundred marking files, fonts and logos.
- Available in 15 languages.

For permanent identification / marking / lettering of batch and series production parts of different materials (steel, stainless steel, aluminium, copper, brass, plastics, tool steel, hardened steels up to 62 HRC, etc.).

- Powerful electro-magnetic marking needle drive.
- Simple intuitive software with password protection.
- High-resolution colour display.
- Marking preview for reliable marking.
- Unbreakable housing.
- Interfaces: USB-A, USB-B and Ethernet.
- Font: Dot matrix in a 5×7 or 9×13 grid, font height 1.0 – 10.0 mm and larger.
- Fonts for character heights greater than 10.0 mm on request.
- High-quality double linear guides for precise marking results.
- Round parts can be marked radially and axially, and also in an arc of a circle.

FlyMarker® mini 120/45 18 V. Extremely handy, 100% mobile **cordless manual marking system** with integral keyboard and high-resolution LC colour display. Marking field: 120 × 45 mm.

- More stable guidance system.
- Extra strong attachment magnet (optional).

Supplied with:

Including tool kit, solid carbide marking needle 90° adjustment bracket with non-slip coating, setting gauge, and carrying case. **2×18 V Li-ion rechargeable batteries**, charger.

maximum marker field width: 120 mm

maximum marker field height: 45 mm

Battery voltage: 18 V
Battery capacity: 2 A·h
Weight: 3.2 kg

Technical description

maximum marker field width	120 mm
maximum marker field height	45 mm
Type of product	