



Cutting disc PREMIUM*** EXTRA THIN, Disc Ø: 125mm



Order data

Order number	563406 125
GTIN	9003172442884
Item class	53T

Description

Version:

Special type for cutting **non-ferrous metals such as aluminium, brass, bronze etc.**

Application:

For freehand cutting using electric and pneumatic angle grinders with maximum 80 m/s peripheral cutting speed v_c .

Specification:

A60N-BFP.

Note:

The disc thickness should be at least 20% of the material thickness to be cut.

Technical description

Shape description	flat
Disc thickness	1 mm
Specification	A60N-BFP
Disc Ø	125 mm

Bore Ø	22.23 mm
for material thicknesses	3 - 5 mm
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
recommended approach angle	90 degrees
optimised for material	Aluminium
optimised for material	Non-ferrous metals
Propulsive equipment	Angle grinders
maximum circumferential speed	80 m/s
Type of product	Cutting disc

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
CuZn	suitable		
dry	suitable		