

**Garant****Table trolley T9 with 2 trays, Type: TL92****Order data**

Order number	918554 TL92
GTIN	4045197967657
Item class	91T

**Description****Version:**

Welded steel design.

Handle with Haptoprene® inlay and impact resistant polypropylene.

2 fixed wheels and 2 castors (with parking brake) with treadless polyurethane tyres and roller bearings.

With 2 securely welded oil-tight trays 37 mm high edge.

An additional shelf is available for insertion as a middle shelf.

**Standard:**

**EN 1757-3**

**Optional extras:**

Intermediate shelf No. 918575; perforated panel No. 918580. Not supplied.

**Colour:**

Silver **powder-coated.**

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

**Technical description**

Platform area depth	500 mm
---------------------	--------

Height of bottom shelf	195 mm
Type	TL92
Depth	509 mm
Platform area width	850 mm
Wheel Ø	125 mm
Load capacity of top shelf	200 kg
Weight	34 kg
Material of wheel	Polyurethane tyres
Width	1040 mm
Number of fixed wheels without parking brake	2
Height	875 mm
Height of top shelf	850 mm
maximum load capacity	250 kg
Number of castors with parking brake	2
Tray height	37 mm
Type of product	Table trolleys