

Garant**Table trolley T9 with 2 trays, Type: TL96****Order data**

Order number	918554 TL96
GTIN	4045197967664
Item class	91T

Description**Version:**

Welded steel design.

Handle with Haptoprene® inlay and impact resistant polypropylene.

2 fixed wheels and 2 castors (with parking brake) with treadless polyurethane tyres and roller bearings.

With 2 securely welded oil-tight trays 37 mm high edge.

An additional shelf is available for insertion as a middle shelf.

Standard:

EN 1757-3

Optional extras:

Intermediate shelf No. 918575; perforated panel No. 918580. Not supplied.

Colour:

Silver **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Material of wheel	Polyurethane tyres
Number of fixed wheels without parking brake	2

Height of top shelf	935 mm
Number of castors with parking brake	2
Width	1190 mm
Wheel Ø	200 mm
Height of bottom shelf	280 mm
maximum load capacity	500 kg
Platform area depth	700 mm
Height	955 mm
Depth	709 mm
Type	TL96
Load capacity of top shelf	200 kg
Platform area width	1000 mm
Weight	56 kg
Tray height	37 mm
Type of product	Table trolleys