

**uvex****Shoe, black/orange uvex 2, S3, EU shoe size: 47**

## Order data

|              |               |
|--------------|---------------|
| Order number | 092132 47     |
| GTIN         | 4031101653167 |
| Item class   | 04V           |

## Description

### Version:

Lightweight and flexible safety shoe. Suitable for wearers allergic to chromium. Width 11.

- **Distance Mesh lining material.**
- **100 % metal-free uvex xenova® toecap.**
- **Two-layer PU sole with TPU inserts with the best damping characteristics.**
- **PU overcap to protect the upper material, for significantly longer working life.**
- **Virtually seamless design to avoid pressure points.**
- **ESD security.**

Safety shoes with hydrophobic micro-velour uppers and elastic laces with quick release fastener.

### Standard:

EN ISO 20345:2011 S3 SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

electrostatic characteristic: EGB/ESD

Protection class: S3

Material of protective toe-cap: Komposit

Puncture resistance: Tekstil

Standard: Inlay type-tested according to DGUV regulation 191

## Technical description

|                  |    |
|------------------|----|
| EU shoe size     | 47 |
| Protection class | S3 |

|                                |  |
|--------------------------------|--|
| Material of protective toe-cap | Komposit   |
| Standard                       | Inlay type-tested according to DGUV regulation 191 |
| Puncture resistance            | Tekstil  |
| Gender                         | Gentlemen's  |
| electrostatic characteristic   | EGB/ESD  |
| Type of product                | Safety shoes                                       |