

**uvex****Shoe, black/orange uvex 2, S3, EU shoe size: 49**

## Order data

Order number	092132 49
GTIN	4031101653181
Item class	04V

## Description

### Version:

Lightweight and flexible safety shoe. Suitable for wearers allergic to chromium. Width 11.

- **Distance Mesh lining material.**
- **100 % metal-free uvex xenova® toecap.**
- **Two-layer PU sole with TPU inserts with the best damping characteristics.**
- **PU overcap to protect the upper material, for significantly longer working life.**
- **Virtually seamless design to avoid pressure points.**
- **ESD security.**

Safety shoes with hydrophobic micro-velour uppers and elastic laces with quick release fastener.

### Standard:

EN ISO 20345:2011 S3 SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

electrostatic characteristic: EGB/ESD

Protection class: S3

Material of protective toe-cap: Komposit

Puncture resistance: Tekstil

Standard: Inlay type-tested according to DGUV regulation 191

## Technical description

Standard

Inlay type-tested according  
to DGUV regulation 191

Protection class	S3
EU shoe size	49
Puncture resistance	Tekstil
Material of protective toe-cap	Komposit
Gender	Gentlemen's
electrostatic characteristic	EGB/ESD
Type of product	Safety shoes