

uvex

Lace-up boot, black/orange uvex 2, S3, EU shoe size: 40



Order data

Order number	092133 40
GTIN	4031101653273
Item class	04V

Description

Version:

Lightweight and flexible safety shoe. Suitable for wearers allergic to chromium. Width 11.

- **Distance Mesh lining material.**
- **100 % metal-free uvex xenova® toecap.**
- **Two-layer PU sole with TPU inserts with the best damping characteristics.**
- **PU overcap to protect the upper material, for significantly longer working life.**
- **Virtually seamless design to avoid pressure points.**
- **ESD security.**

Lace-up boots with hydrophobic high-tech micro-velour uppers and soft padded collar and padded tongue.

Standard:

EN ISO 20345:2011 S3 SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

electrostatic characteristic: EGB/ESD

Protection class: S3

Material of protective toe-cap: Komposit

Puncture resistance: Tekstil

Standard: Inlay type-tested according to DGUV regulation 191

Technical description

Standard	Inlay type-tested according to DGUV regulation 191
Puncture resistance	Tekstil
Material of protective toe-cap	Komposit
EU shoe size	40
Protection class	S3
Gender	Gentlemen's
electrostatic characteristic	EGB/ESD
Type of product	Safety boots