

# uvex

## Shoe, black/orange uvex 2, S3, EU shoe size: 35



### Order data

|              |               |
|--------------|---------------|
| Order number | 092132 35     |
| GTIN         | 4031101653044 |
| Item class   | 04V           |

### Description

#### Version:

Lightweight and flexible safety shoe. Suitable for wearers allergic to chromium. Width 11.

- **Distance Mesh lining material.**
- **100 % metal-free uvex xenova® toecap.**
- **Two-layer PU sole with TPU inserts with the best damping characteristics.**
- **PU overcap to protect the upper material, for significantly longer working life.**
- **Virtually seamless design to avoid pressure points.**
- **ESD security.**

Safety shoes with hydrophobic micro-velour uppers and elastic laces with quick release fastener.

#### Standard:

EN ISO 20345:2011 S3 SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

electrostatic characteristic: EGB/ESD

Protection class: S3

Material of protective toe-cap: Komposit

Puncture resistance: Tekstil

Standard: Inlay type-tested according to DGUV regulation 191

### Technical description

|          |                                                    |
|----------|----------------------------------------------------|
| Standard | Inlay type-tested according to DGUV regulation 191 |
|----------|----------------------------------------------------|

|                                |              |
|--------------------------------|--------------|
| Material of protective toe-cap | Komposit     |
| EU shoe size                   | 35           |
| Puncture resistance            | Tekstil      |
| Protection class               | S3           |
| Gender                         | Gentlemen's  |
| electrostatic characteristic   | EGB/ESD      |
| Type of product                | Safety shoes |